

LUPA ILUMINADA LED

Ref. 100287-5X

Características:

- Lente de vidrio de alta transmisión y resistencia al rayado.
- 90 LEDs blancos, baja temperatura y larga duración.
- Montaje estándar: sargento para mesa.
- Alimentación eléctrica mediante rectificador electrónico especialmente estable.
- La lente puede orientarse hacia cualquier superficie.
- Brazo ajustable de fácil posicionamiento.

Especificaciones:

- Lupa: Ø120 mm, 5 dioptrías.
- Alimentación: 220-240 V, 50 Hz.
- Iluminación: 90 LEDs blancos.
- 6500 K – 350 Lumen.
- Balasto electrónico.

Uso:

- Antes del uso, retirar todo el embalaje.
- Colocar la lámpara en una superficie horizontal.
- Conectar a una fuente de alimentación eléctrica adecuada.
- Encender mediante el interruptor ON/OFF situado en la superficie de la base.
- Colocar la lupa en la posición deseada.

Precauciones de seguridad:

- Solo para uso interior.
- Temperatura ambiente: -20~40 °C
- Humedad: ≤ 95 %
- El aparato solo debe ser desmontado por un técnico cualificado.
- Para cualquier reparación, desconectar previamente de la alimentación eléctrica.
- No dejar nunca la lente sin vigilancia bajo la incidencia de la luz solar o de otro tipo. Esto supone un riesgo de incendio.

LED MAGNIFYING GLASS

Ref. 100287-5X

Characteristics:

- Glass lens with high transmittance and not easy to scratch.
- Light source by 90 pcs white LED, low temperature and long life.
- Standard mount: desktop clamp.
- Power supplied with electronic rectifier provides even more stable performance.
- The universal joint neck design allows the lens face to any side you prefer.
- Adjustable arm for easy positioning where it is most needed.

Specifications:

- Magnifier: Ø120 mm, 5 diopter.
- Power supply: 220-240 V, 50 Hz.
- Light source: 90 pcs white LED.
- 6500 K – 350 Lumen.
- Supplied with electronic ballast.

Use:

- Before use, remove all packing foam around the lamp.
- Put the lamp on the horizontal table.
- Insert the plug into a conveniently located electrical socket.
- Switch on using the ON/OFF switch located on the surface of the base.
- Place the head in the desired position.

Safe cautions:

- Indoor use only.
- Environment temperature: -20~40 °C
- Humidity: ≤ 95 %
- Never disassemble the magnifier lamp unless you are a qualified technician.
- Plug must be taken out while repairing the magnifier lamp.
- Never leave the lens unattended in direct sunlight or where light can shine through it. This constitutes a fire hazard.

IMPORTADO POR



MESTRA®

TALLERES MESTRAITUA S.L.

Txori-Erri Etorbidea, 60

Tel. +34 944530388 - Fax +34 944711725

mestra@mestra.es - www.mestra.es

48150 SONDIKA – BILBAO – ESPAÑA